



PRESSURIZED GRAVURE HEAD

Overview

Davis-Standard's Pressurized Gravure Head (PGH) was developed to further enhance gravure coating by realizing and overcoming gravure deficiencies. The design of the PGH implements fluid flow dynamics and die technology. The PGH applies air free coating to the substrate or transfer roller. Davis-Standard's PGH allows for increased coatweight, increased production speed, reduced air entrainment, and removal of contaminants.

Features


- Change Coatweights Easily
- Control Coating Flow
- Reduced Air Entrainment
- Increased Gravure Speeds
- Web Widths up to 160" (4064 mm) Wide
- Line Speeds up to 3000 fpm (914.4 mpm)
- Solvent, Water-Based, and 100% Solid Coatings


PRESSURIZED GRAVURE HEAD

DENSITY CHART

Flow Rate (A) GPM		4.44	5.54	6.67	7.50	8.00
Density to Head (C)	9.10	9.20	8.92	8.91	8.95	8.65
Return (B) Flow GPM		0.63	0.99	1.44	1.98	2.44
Return (B) Density	9.00	7.77	8.30	8.50	8.63	8.64

DIAGRAM OF DENSITY SAMPLE SETUP





DOCTOR BLADE BLADE RETAINER SIDE PLATE



1 Extrusion Drive > Pawcatuck > CT > 06379-2313 > USA TEL +1 860-599-1010 FAX +1 860-599-6258

davis-standard.com